

TOULOUSE BLAGNAC

PRECODING INA RNAV (GNSS) RWY 14L

| INA RNAV(GNSS) RWY 14L |                                                                                                                  |                 |                         |          |                   |                    |               |                |                              |                              |              |                               |                          |
|------------------------|------------------------------------------------------------------------------------------------------------------|-----------------|-------------------------|----------|-------------------|--------------------|---------------|----------------|------------------------------|------------------------------|--------------|-------------------------------|--------------------------|
| RMK                    | GNSS only - Linked to FNA RNP 14L and FNA ILS ou/ or LOC RWY 14L<br><i>Procedure developed under CDO concept</i> |                 |                         |          |                   |                    |               |                | MAG VAR 2020 01.0°E          |                              |              | REF NAVAID :                  |                          |
|                        | Leg sequence                                                                                                     | Path Terminator | Waypoint Identification | Fly Over | Direction MAG (°) | Direction True (°) | Distance (NM) | Turn direction | MNM Altitude (FL or AMSL ft) | MAX Altitude (FL or AMSL ft) | MAX IAS (kt) | Vertical angle (°) / TCH (ft) | Navigation Accuracy (NM) |
| HLDG                   | -                                                                                                                | ADIMO           | -                       | -        | -                 | -                  | -             | -              | -                            | -                            | -            | -                             | -                        |
| HLDG                   | -                                                                                                                | FUZAP           | -                       | -        | -                 | -                  | -             | -              | -                            | -                            | -            | -                             | -                        |
| HLDG                   | -                                                                                                                | SURAS           | -                       | -        | -                 | -                  | -             | -              | -                            | -                            | -            | -                             | -                        |
| INA ADIMO              | IF                                                                                                               | ADIMO           | -                       | -        | -                 | -                  | -             | -              | FL080                        | -                            | -            | -                             | -                        |
|                        | TF                                                                                                               | BO506           | -                       | 307      | 308.2             | 24.6               | -             | -              | FL080                        | -                            | -            | -                             | 1.0                      |
|                        | TF                                                                                                               | BO509           | -                       | 307      | 307.9             | 11.7               | L             | -              | 4000                         | -                            | -            | -                             | 1.0                      |
|                        | TF                                                                                                               | IO14L           | -                       | 205      | 205.8             | 5.1                | -             | -              | 3000                         | -                            | 210          | -                             | 1.0                      |
| INA AGN                | IF                                                                                                               | AGN             | -                       | -        | -                 | -                  | -             | -              | FL080                        | -                            | -            | -                             | -                        |
|                        | TF                                                                                                               | BO508           | -                       | 095      | 096.0             | 10.3               | -             | -              | -                            | -                            | -            | -                             | 1.0                      |
|                        | TF                                                                                                               | IO14L           | -                       | 140      | 141.2             | 6.3                | -             | -              | 3000                         | -                            | 210          | -                             | 1.0                      |
|                        | IF                                                                                                               | FUZAP           | -                       | -        | -                 | -                  | -             | -              | FL080                        | -                            | -            | -                             | -                        |
| INA FUZAP              | TF                                                                                                               | BO509           | -                       | 230      | 230.8             | 11.1               | -             | -              | 4000                         | -                            | -            | -                             | 1.0                      |
|                        | TF                                                                                                               | IO14L           | -                       | 205      | 205.8             | 5.1                | -             | -              | 3000                         | -                            | 210          | -                             | 1.0                      |
|                        | IF                                                                                                               | SURAS           | -                       | -        | -                 | -                  | -             | -              | FL080                        | -                            | -            | -                             | -                        |
| INA SURAS              | TF                                                                                                               | BO507           | -                       | 004      | 005.2             | 7.7                | -             | -              | -                            | -                            | -            | -                             | 1.0                      |
|                        | TF                                                                                                               | IO14L           | -                       | 077      | 078.3             | 5.4                | -             | -              | 3000                         | -                            | 210          | -                             | 1.0                      |